

Micromax™ 5747

Electronic Inks and Pastes

Gold Via Fill Conductor

Gold conductor Micromax™ 5747 is a cadmium free via fill composition. It is used to fill vias in high density multi-layer gold hybrids.

Product benefits

- Cadmium free gold conductor
- Capable of via filling two to three dielectric layers with a single print
- Good top surface co planarity when used with Micromax™ multi-layer dielectrics

Product information

Solvent or thinner	Micromax™ 4577
Solid content	84.5 - 86.5 ^[1] %
[1]: 750 °C	

Rheological properties

Viscosity	180 - 230 ^[2] Pa.s
[2]: Brookfield HAT, US&SP SC4-14/6R, 10 rpm, 25 °C	

Application technique

Mask mesh	325
Drying time	10 - 15 min
Drying temperature	150 °C
Theoretical coverage	64 ^[3] cm ² /g
Leveling time	5 - 10 min

[3]: based on an average dried thickness of 15µm

Storage and stability

Shelf life	6 ^[4] months
------------	-------------------------

[4]: in unopened containers, from date of shipment, at temperature <25 °C

Additional information

How to use

Processing

• Substrates

- Properties are based on tests on 96% alumina substrates. Substrates of other compositions and from various manufacturers may result in variations in performance properties, as may different lots of substrates, and any subsequent processing of

Micromax™ 5747

Electronic Inks and Pastes

substrates (e.g. laser scribing or drilling) prior to printing.

- It is the responsibility of users to determine the effects of any of the above variable in their particular situations.

• Printing

- Micromax™ 5747 conductor composition should be thoroughly mixed before use. This is best achieved by slow, gentle hand stirring with a clean, burr-free spatula (flexible plastic) for 30 seconds - 1 minute. Printing should be carried out in a clean, well-ventilated area.
- Note : Optimum printing characteristics of Micromax™ 5747 are generally achieved in the temperature range 20°C - 23°C. It is therefore important that the material, in its container, is at this temperature prior to commencement of printing. For best via fill a 325 mesh stainless steel screen is recommended.

• Drying

- Allow prints to level for 5-10 minutes at room temperature in a clean environment, followed by drying for 10-15 minutes at 150°C in a well ventilated oven or conveyor dryer.

• Firing

- Micromax™ 5747 may be fired in either a 30 or 60 minutes firing cycle to a peak temperature of 850°C held for 10 minutes. Care must be taken to ensure that any gases/vapors from other chemicals/materials (e.g. halogenated solvents) do not enter the furnace muffle. It is also essential that the air supply to the furnace is clean, dry and free of contaminants.
- Air flows and extraction rates should be optimized to ensure that oxidizing conditions exist within the muffle, and that no furnace exhaust gases enter the room.

Properties

- Information in this datasheet shows anticipated typical physical properties for Micromax™ 5747 based on specific controlled experiments in our labs and are not intended to represent the product specifications, details of which are available upon request.

Storage and shelf life

Containers should be stored, tightly sealed, in a clean, stable environment at room temperature (<25°C). Shelf life of material in unopened containers is six months from date of shipment. Some settling of solids may occur and compositions should be thoroughly mixed prior to use.

Micromax™ 5747

Electronic Inks and Pastes

Safety and handling

For safety and handling information pertaining to this product, read Safety Data Sheet (SDS).

NOTICE TO USERS: Values shown are based on testing of laboratory test specimens and represent data that fall within the standard range of properties for natural material. These values alone do not represent a sufficient basis for any part design and are not intended for use in establishing maximum, minimum, or ranges of values for specification purposes. Colourants or other additives may cause significant variations in data values. Properties of moulded parts can be influenced by a wide variety of factors including, but not limited to, material selection, additives, part design, processing conditions and environmental exposure. Other than those products expressly identified as medical grade (including by MT® product designation or otherwise), Celanese's products are not intended for use in medical or dental implants. Regardless of any such product designation, any determination of the suitability of a particular material and part design for any use contemplated by the users and the manner of such use is the sole responsibility of the users, who must assure themselves that the material as subsequently processed meets the needs of their particular product or use. To the best of our knowledge, the information contained in this publication is accurate; however, we do not assume any liability whatsoever for the accuracy and completeness of such information. The information contained in this publication should not be construed as a promise or guarantee of specific properties of our products. It is the sole responsibility of the users to investigate whether any existing patents are infringed by the use of the materials mentioned in this publication. Moreover, there is a need to reduce human exposure to many materials to the lowest practical limits in view of possible adverse effects. To the extent that any hazards may have been mentioned in this publication, we neither suggest nor guarantee that such hazards are the only ones that exist. We recommend that persons intending to rely on any recommendation or to use any equipment, processing technique or material mentioned in this publication should satisfy themselves that they can meet all applicable safety and health standards. We strongly recommend that users seek and adhere to the manufacturer's current instructions for handling each material they use, and entrust the handling of such material to adequately trained personnel only. Please call the telephone numbers listed for additional technical information. Call Customer Services for the appropriate Materials Safety Data Sheets (MSDS) before attempting to process our products.

© 2023 Celanese or its affiliates. All rights reserved. Celanese®, registered C-ball design and all other trademarks identified herein with ®, TM, SM, unless otherwise noted, are trademarks of Celanese or its affiliates. Fortron is a registered trademark of Fortron Industries LLC. KEPITAL is a registered trademark of Korea Engineering Plastics Company, Ltd.