

Technical Data Sheet

Staybelite™ Ester 10-E Ester of Hydrogenated Rosin

Applications

- Adhesives/sealants-b&c
- Bookbinding
- Caps & lids non-food contact
- Carpet construction
- Case & carton sealing closings
- Commerical printing inks
- Film modification
- Labels non food contact
- Packaging component films
- Packaging components non food contact
- Packaging tape
- Paints & coatings
- Polymer modification
- Protective coatings
- Road markings
- Roofing ingredients
- Solder flux
- Specialty tape
- Tape non food contact
- Tires
- Wax ingredients
- Wire/cable

Key Attributes

- Easily emulsifiable
- Excellent resistance to oxidation
- Light color
- Low odor
- Medium softening point
- Thermoplastic hydrogenated resin
- Wide solubility and compatibility range

Product Description

Staybelite™ Ester 10-E Ester of Hydrogenated Rosin is a pale, thermoplastic resin with the excellent resistance to oxidation and discoloration characteristic of ester resins derived from hydrogenated rosin. It is a glycerol ester of rosin that has been stabilized by hydrogenation and has found wide acceptance as a tackifying resin for many adhesive applications, particularly pressure-sensitive, hot melt and emulsion types. In general, it is useful where there is need for a pale, nonoxidizing, color-stable resin.

Typical Properties

Property	Test Method	Typical Value, Units
General		
Ring and Ball Softening Point	ASTM E 28	86 °C
Color, Gardner ^a		6
Acid Number (mg KOH/g)		9
Density		
@ 25°C		1.07 kg/dm ³
Melt Viscosity		
@ 120°C		1800 cP
@ 140°C		330 cP
@ 160°C		90 cP
Description, Base Resin		Partially Hydrogenated Gum Rosin

^a50% resins solids in toluene or xylene

Compatibility and Solubility

Compatible at all ratios, or in limited but practically useful proportions, with other resins, waxes, and plasticizers; with natural and synthetic rubbers, chlorinated rubber, and ethylcellulose; with EVA (ethylene-vinyl acetate) copolymers and low molecular weight polyethylene; with SIS (styrene-isoprene-styrene) and SBS (styrene-butadiene-styrene) block copolymers; with APAO (amorphous poly-alphaolefins); with acrylic resins; with certain polyamide resins and polyurethane compounds; and with PVP (polyvinylpyrrolidone), polyvinylbutyral, nitrocellulose, drying oils and alkyd resins.

Soluble in esters; ketones; higher alcohols; glycol ethers; and aliphatic, aromatic, and chlorinated hydrocarbons. Insoluble in ethanol and water. Solubility Parameters, 50% resin concentration: 7,0-10,6 in Class I solvents - weakly hydrogen-bonded; 7,4-10,0 in Class II solvents - moderately hydrogen-bonded; 9,5-11,9 in Class III solvents - strongly hydrogen-bonded.

Packaging

Staybelite™ Ester 10-E Ester of Hydrogenated Rosin is pastillated and packed in polyethylene bags of 25 kg net, and supplied on shrink-wrapped pallets of 40 bags (1000 kg) each, from Eastman's facilities in the Netherlands and from warehouses located in Europe.

Storage

Due to the thermoplastic behavior, pastillated and flaked resins may fuse, block or lump. This can be accelerated under any of the following conditions: 1) above ambient temperature, 2) prolonged storage, 3) pressure, e.g., stacking pallets, or a combination of these conditions. This is particularly applicable for low softening point resin grades.

In order to maintain the flake or pastille shape, we therefore recommend storing the material in a temperature-controlled area, be careful with stacking material or applying pressure and preventing prolonged storage.

It should be noted that lumping does not have a negative impact on the product specifications. Due to the nature of the product, claims regarding lumping cannot be accepted.

Resins are prone to gradual oxidation, some more so than others. This could result in darkening and/or it could have an adverse effect on the solubility of the resin in organic solvents or on its compatibility with polymers. Accordingly, it is recommended that strict control of inventory be observed at all times, taking care that the oldest material is used first.

Staybelite™ Ester 10-E Ester of Hydrogenated Rosin material will remain within product specification limits for a period of at least twelve months after shipment from Eastman's production facilities in the Netherlands, provided storage conditions outlined in this data sheet are observed. However, as we can neither anticipate the conditions under which the resin is processed nor the end use applications for which it is used, we recommend that the material be tested upon receipt.

Eastman and its marketing affiliates shall not be responsible for the use of this information, or of any product, method, or apparatus mentioned, and you must make your own determination of its suitability and completeness for your own use, for the protection of the environment, and for the health and safety of your employees and purchasers of your products. No warranty is made of the merchantability of fitness of any product, and nothing herein waives any of the Seller's conditions of sale.

2/28/2018 11:35:39 AM