



Bergaflex™ BFI 95A-3120

Thermoplastic Elastomer

Key Characteristics

Product Description

Bergaflex™ BFI 95A-3120 is an easy processing, general purpose TPE.
Material is semi filled, opaque and has therefore a medium density.

General

Material Status	• Commercial: Active		
Regional Availability	• Asia Pacific	• Europe	• North America
Features	• General Purpose	• Good Processability	
Uses	• Appliances • Automotive Applications	• Consumer Applications • General Purpose	• Industrial Applications
RoHS Compliance	• RoHS Compliant		
Appearance	• Black		
Forms	• Pellets		
Processing Method	• Injection Molding		

Technical Properties ¹

Physical	Typical Value (English)	Typical Value (SI)	Test Method
Density / Specific Gravity	0.990	0.990	ISO 1183
Elastomers	Typical Value (English)	Typical Value (SI)	Test Method
Tensile Stress ²			ISO 37
Break, 73°F (23°C), 0.0787 in (2.00 mm)	1890 psi	13.0 MPa	
Tensile Elongation ²			ISO 37
Break, 73°F (23°C), 0.0787 in (2.00 mm)	600 %	600 %	
Compression Set (73°F (23°C), 72 hr)	40 %	40 %	ISO 815
Hardness	Typical Value (English)	Typical Value (SI)	Test Method
Durometer Hardness ³			ISO 7619
Shore A, 10 sec, 73°F (23°C), Injection Molded	95	95	

Processing Information

Injection	Typical Value (English)	Typical Value (SI)
Suggested Max Regrind	20 %	20 %
Rear Temperature	329 to 347 °F	165 to 175 °C
Middle Temperature	347 to 383 °F	175 to 195 °C
Front Temperature	365 to 437 °F	185 to 225 °C
Nozzle Temperature	383 to 437 °F	195 to 225 °C
Mold Temperature	68 to 104 °F	20 to 40 °C
Back Pressure	290 to 1450 psi	2.00 to 10.0 MPa
Screw Speed	40 to 100 rpm	40 to 100 rpm

Injection Notes

Purge thoroughly before and after use of this product with a low flow (0.5 - 2.5 MFR) polyethylene (PE) or polypropylene (PP).

Bergaflex™ BFI 95A-3120 has excellent melt stability. Maximum residence times may vary, depending on the size of the barrel. Generally, the barrel should be emptied if it is idle for periods of 8 - 10 minutes or longer.

Drying is not Required

Injection Speed: 1 to 3 in/sec

1st Stage - Boost Pressure: 350 to 900 psi

2nd Stage - Hold Pressure: 30% of Boost

Hold Time (Thick Part): 3 to 10 sec

Hold Time (Thin Part): 1 to 3 sec

Notes

¹ Typical values are not to be construed as specifications.

² 7.9 in/min (200 mm/min)

³ ±5 Sh A



Beyond Polymers.

Better Business Solutions. SM