



# Versaflex™ CL E90

## Thermoplastic Elastomer

### Key Characteristics

#### Product Description

Versaflex™ CL E90 is an exceptional clarity, high performance and autoclavable solution ideal for healthcare and food packaging. Versaflex™ CL E90 is also formulated without the use of plasticizers.

New Product. Commercial specifications have not been established.

- Flexible
- Formulated without Plasticizers
- High Clarity

#### General

Material Status	• Commercial: Active
Regional Availability	• Africa & Middle East • Asia Pacific • Latin America • North America
Features	• Good Flexibility • High Clarity
Uses	• Bottles • Film • Medical/Healthcare Applications • Personal Care
Agency Ratings	• FDA 21 CFR 177.1210 <sup>1</sup> • ISO 10993 Part 4 • ISO 10993 Part 5 • USP Class VI <sup>2</sup>
RoHS Compliance	• RoHS Compliant
Appearance	• Clear/Transparent
Forms	• Pellets
Processing Method	• Extrusion

### Technical Properties<sup>3</sup>

Physical	Typical Value (English)	Typical Value (SI)	Test Method
Specific Gravity	0.900	0.900	ASTM D792
Films	Typical Value (English)	Typical Value (SI)	Test Method
Oxygen Permeability			ASTM D3985
70°F (21°C), 4.7 mil (120 µm)	710 cm <sup>3</sup> ·mil/100in <sup>2</sup> /atm/24 hr	280 cm <sup>3</sup> ·mm/m <sup>2</sup> /atm/24 hr	
70°F (21°C), 73 mil (1800 µm)	660 cm <sup>3</sup> ·mil/100in <sup>2</sup> /atm/24 hr	260 cm <sup>3</sup> ·mm/m <sup>2</sup> /atm/24 hr	
Oxygen Transmission Rate			ASTM D3985
70°F (21°C), 4.7 mil (120 µm)	150 cm <sup>3</sup> /100 in <sup>2</sup> /24 hr	2300 cm <sup>3</sup> /m <sup>2</sup> /24 hr	
70°F (21°C), 73 mil (1800 µm)	9.2 cm <sup>3</sup> /100 in <sup>2</sup> /24 hr	140 cm <sup>3</sup> /m <sup>2</sup> /24 hr	
Elastomers	Typical Value (English)	Typical Value (SI)	Test Method
Tensile Stress <sup>4,5</sup> (100% Strain, 73°F (23°C))	1000 psi	6.89 MPa	ASTM D412
Tensile Stress <sup>4,5</sup> (300% Strain, 73°F (23°C))	1230 psi	8.51 MPa	ASTM D412
Tensile Strength <sup>4,5</sup> (Break, 73°F (23°C))	1830 psi	12.6 MPa	ASTM D412
Tensile Elongation <sup>4,5</sup> (Break, 73°F (23°C))	570 %	570 %	ASTM D412

Copyright © 2016 PolyOne Corporation. PolyOne makes no representations, guarantees, or warranties of any kind with respect to the Information contained in this document about its accuracy, suitability for particular applications, or the results obtained or obtainable using the information. Some of the Information arises from laboratory work with small-scale equipment which may not provide a reliable indication of performance or properties obtained or obtainable on larger-scale equipment. Values reported as "typical" or stated without a range do not state minimum or maximum properties; consult your sales representative for property ranges and min/max specifications. Processing conditions can cause material properties to shift from the values stated in the Information. PolyOne makes no warranties or guarantees respecting suitability of either PolyOne's products or the Information for your process or end-use application. You have the responsibility to conduct full-scale end-product performance testing to determine suitability in your application, and you assume all risk and liability arising from your use of the Information and/or use or handling of any product. POLYONE MAKES NO WARRANTIES, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, IMPLIED WARRANTIES OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE, either with respect to the Information or products reflected by the Information. This data sheet shall NOT operate as permission, recommendation, or inducement to practice any patented invention without permission of the patent owner.

Elastomers	Typical Value (English)	Typical Value (SI)	Test Method
Compression Set			ASTM D395B
72°F (22°C), 22 hr	27 %	27 %	
158°F (70°C), 22 hr	67 %	67 %	
212°F (100°C), 22 hr	73 %	73 %	
Hardness	Typical Value (English)	Typical Value (SI)	Test Method
Durometer Hardness (Shore A, 10 sec)	90	90	ASTM D2240
Fill Analysis	Typical Value (English)	Typical Value (SI)	Test Method
Apparent Viscosity			ASTM D3835
392°F (200°C), 1340 sec <sup>-1</sup>	162 Pa·s	162 Pa·s	
392°F (200°C), 11200 sec <sup>-1</sup>	34.0 Pa·s	34.0 Pa·s	

### Processing Information

Extrusion	Typical Value (English)	Typical Value (SI)
Melt Temperature	360 to 400 °F	182 to 204 °C
Die Temperature	340 to 390 °F	171 to 199 °C

#### Extrusion Notes

Color concentrates with polypropylene (PP), ethylene vinyl acetate (EVA), or low density polyethylene (PE) carriers are most suitable for coloring Versaflex™ CL E90. Improved color dispersion can be achieved by using higher melt flow concentrates (with a melt flow from 25 - 40g/10 min). Typical loadings for color concentrates are 1% to 5% by weight. Liquid color can be used, but mineral oil based carriers may have a significant effect on the final hardness value. Concentrates based on PVC should not be used. A high color match consistency can be obtained by using precolored compounds available from GLS. The final determination of color concentrate suitability should be determined by customer trials.

Purge thoroughly before and after use of this product with a low flow (0.5 - 2.5 MFR) polyethylene (PE) or polypropylene (PP).

Drying is not Required.

Rear Zone = 330-370F

Center Zone = 350-400F

Front Zone = 360-420F

Screw Speed = 100-500 RPM

#### Notes

<sup>1</sup> Please contact GLS Thermoplastic Elastomers for a copy of the FDA compliance letter.

<sup>2</sup> Please contact PolyOne GLS Thermoplastic Elastomers for a complete copy of the GLS Healthcare Policy.

1. The Customer must notify GLS of any FDA Class I and/or European Union Class I medical devices for each specific product and application.

2. The Customer shall not knowingly manufacture, use, sell or otherwise supply, directly or indirectly products or compounds made from GLS products in any of the following without prior written approval by GLS for each specific product or application:

a. Cosmetics

b. Drugs and other Pharmaceuticals

c. Temporary or permanent implantation in the human body, regardless of the intended duration of implantation

d. Class II and Class III Medical Devices as defined in 21 CFR 860.3 ("Medical Devices")

e. Class IIa, IIb and III as defined in Directive 93/42/EEC

<sup>3</sup> Typical values are not to be construed as specifications.

<sup>4</sup> Die C

<sup>5</sup> 2 hr