



# Edgetek™ PC-30GF/000 BK088

## Polycarbonate

### Key Characteristics

Product Description	
30% glass fiber reinforced polycarbonate compound.	
General	
Material Status	• Commercial: Active
Regional Availability	• Asia Pacific
Filler / Reinforcement	• Glass Fiber, 30% Filler by Weight
Appearance	• Black
Processing Method	• Injection Molding

### Technical Properties <sup>1</sup>

Physical	Typical Value (English)	Typical Value (SI)	Test Method
Density / Specific Gravity	1.41	1.41	ASTM D792
Molding Shrinkage - Flow	1.0E-3 to 3.0E-3 in/in	0.10 to 0.30 %	ASTM D955
Mechanical	Typical Value (English)	Typical Value (SI)	Test Method
Tensile Strength <sup>2</sup>	16700 psi	115 MPa	ASTM D638
Flexural Modulus <sup>3</sup>	1.20E+6 psi	8250 MPa	ASTM D790
Flexural Strength <sup>3</sup>	26100 psi	180 MPa	ASTM D790
Impact	Typical Value (English)	Typical Value (SI)	Test Method
Notched Izod Impact			ASTM D256
73°F (23°C), 0.126 in (3.20 mm)	2.7 ft-lb/in	150 J/m	
Thermal	Typical Value (English)	Typical Value (SI)	Test Method
Deflection Temperature Under Load			ASTM D648
264 psi (1.8 MPa), Unannealed, 0.126 in (3.20 mm)	284 °F	140 °C	
Electrical	Typical Value (English)	Typical Value (SI)	Test Method
Surface Resistivity	1.0E+15 ohms	1.0E+15 ohms	ASTM D257
Flammability	Typical Value (English)	Typical Value (SI)	Test Method
Flame Rating (0.13 in (3.2 mm))	V-1	V-1	Internal Method

### Processing Information

Injection	Typical Value (English)	Typical Value (SI)
Drying Temperature	230 to 266 °F	110 to 130 °C
Drying Time	3.0 to 4.0 hr	3.0 to 4.0 hr
Rear Temperature	536 to 590 °F	280 to 310 °C
Middle Temperature	536 to 590 °F	280 to 310 °C
Front Temperature	536 to 590 °F	280 to 310 °C
Mold Temperature	176 to 248 °F	80 to 120 °C

Injection Notes
Injection Pressure: MED-HIGH
Hold Pressure: MED-HIGH
Screw Speed: MODERATE
Back Pressure: LOW

**Notes**

<sup>1</sup> Typical values are not to be construed as specifications.

<sup>2</sup> 0.20 in/min (5.0 mm/min)

<sup>3</sup> 0.051 in/min (1.3 mm/min)



*Beyond Polymers.*

*Better Business Solutions. SM*