



Versaflex™ FFC 2882-87

Thermoplastic Elastomer

Key Characteristics

Product Description			
Versaflex™ FFC 2882-87 is designed to pass several food extraction and/or migration conditions identified in applicable U.S., Europe, and China food contact standards. Versaflex™ FFC 2882-87 will also overmold and co-extrude to polypropylene.			
General			
Material Status	• Commercial: Active		
Regional Availability	• Africa & Middle East • Asia Pacific	• Europe • Latin America	• North America
Features	• Food Contact Acceptable		
Uses	• Consumer Applications • Containers	• Gaskets • Kitchenware	• Non-specific Food Applications • Overmolding
Agency Ratings	• EU 10/2011 ¹	• FDA 21 CFR 177.2600 ²	
RoHS Compliance	• RoHS Compliant		
Appearance	• Translucent		
Forms	• Pellets		
Processing Method	• Extrusion	• Injection Molding	

Technical Properties ³

Physical	Typical Value (English)	Typical Value (SI)	Test Method
Density / Specific Gravity	0.880	0.880	ASTM D792
Molding Shrinkage - Flow (Injection Molded)	9.0E-3 to 0.015 in/in	0.90 to 1.5 %	ASTM D955
Elastomers	Typical Value (English)	Typical Value (SI)	Test Method
Tensile Stress ^{4, 5} (100% Strain, 73°F (23°C))	1050 psi	7.25 MPa	ASTM D412
Tensile Stress ^{4, 5} (300% Strain, 73°F (23°C))	1110 psi	7.65 MPa	ASTM D412
Tensile Strength ^{4, 5} (Break, 73°F (23°C))	1310 psi	9.03 MPa	ASTM D412
Tensile Elongation ^{4, 5} (Break, 73°F (23°C))	700 %	700 %	ASTM D412
Hardness	Typical Value (English)	Typical Value (SI)	Test Method
Durometer Hardness (Shore A, 10 sec)	88	88	ASTM D2240
Fill Analysis	Typical Value (English)	Typical Value (SI)	Test Method
Apparent Viscosity 392°F (200°C), 11200 sec ⁻¹	34.8 Pa·s	34.8 Pa·s	ASTM D3835

Processing Information

Injection	Typical Value (English)	Typical Value (SI)
Suggested Max Regrind	20 %	20 %
Rear Temperature	380 to 400 °F	193 to 204 °C
Middle Temperature	390 to 420 °F	199 to 216 °C
Front Temperature	400 to 440 °F	204 to 227 °C
Nozzle Temperature	410 to 460 °F	210 to 238 °C
Processing (Melt) Temp	400 to 440 °F	204 to 227 °C
Mold Temperature	55 to 90 °F	13 to 32 °C
Back Pressure	0.00 to 80.0 psi	0.00 to 0.552 MPa

Injection	Typical Value (English)	Typical Value (SI)
Screw Speed	50 to 100 rpm	50 to 100 rpm

Injection Notes

Color concentrates based on polypropylene (PP), ethylene vinyl acetate (EVA), or low density polyethylene (LDPE) are most suitable for coloring Versaflex™ FFC 2882-87. Improved color dispersion can be achieved by using higher melt flow concentrates (with a melt flow from 25-40 g/10 min). Typical loadings for color concentrates are 1% to 5% by weight. Liquid color can be used, but mineral oil based carriers may have a significant effect on the final hardness value. Concentrates based on PVC should not be used. A high color match consistency can be obtained by the use of precolored compounds available from GLS. The final determination of color concentrate suitability should be determined by customer trials.

Purge thoroughly before and after use of this product with a low flow (0.5 - 2.5 MFR) polyethylene (PE) or polypropylene (PP).

Regrind levels up to 20% can be used with Versaflex™ FFC 2882-87 with minimal property loss, provided that the regrind is free of contamination. To minimize losses during molding, the melt temperature should remain as low as possible. The final determination of regrind effectiveness should be determined by the customer.

Versaflex™ FFC 2882-87 has excellent melt stability. Maximum residence times may vary, depending on the size of the barrel. Generally, the barrel should be emptied if it is idle for periods of 8 - 10 minutes or longer.

Drying is not Required

Injection Speed: 1 to 3 in/sec

1st Stage - Boost Pressure: 500 to 700 psi

2nd Stage - Hold Pressure: 10 to 30% of Boost

Hold Time (Thick Part): 2 to 4 sec

Hold Time (Thin Part): 1 to 2 sec

Extrusion	Typical Value (English)	Typical Value (SI)
Melt Temperature	400 to 440 °F	204 to 227 °C
Die Temperature	420 to 460 °F	216 to 238 °C

Extrusion Notes

Rear: 380-400F

Center: 390-420F

Front: 400-440F

Screw: 100-500rpm

Notes

¹ Please contact GLS Thermoplastic Elastomers for a copy of the EU compliance letter.

² Please contact GLS Thermoplastic Elastomers for a copy of the FDA compliance letter.

³ Typical values are not to be construed as specifications.

⁴ Die C

⁵ 2 hr