

ALCOM PA6 900/8.4 GF10 MR20 BK0002-00

(Last update: 30.01.2025)

MOCOM

Base Polymer	Polyamide 6
Filler/Additive System	10 % glass fibres, 20 % mineral
Special Features	heat stabilised, easy flow
Typical Applications	housings, functional components

Pre-Drying Conditions	80 °C in a dry air (dessiccant) dryer for 2-12 h dependant on moisture content
Processing Injection Moulding	melt temperature 270-290 °C mould temperature 80-100 °C
Storage	dry, protected from light

Properties	dry/cond.	Dimension	Test Norm
Mechanical Properties			
Flexural Modulus	7400 / 5800	MPa	ISO 178
Flexural Strength	170 / 120	MPa	ISO 178
Tensile Modulus	8200 / 5500	MPa	ISO 527
Tensile Strength at Break	110 / 65	MPa	ISO 527
Tensile Elongation at Break	2.6 / 6.5	%	ISO 527
Impact Strength (Charpy, 23°C)	45 / 40	kJ/m ²	ISO 179/1eU
Impact Strength (Charpy, -40°C)	40 / -	kJ/m ²	ISO 179/1eU
Notched Impact Strength (Charpy, 23°C)	5 / 5	kJ/m ²	ISO 179/1eA
Notched Impact Strength (Charpy, -40°C)	3 / -	kJ/m ²	ISO 179/1eA
Thermal Properties			
HDT / A (1,8 MPa)	200 / *	°C	ISO 75-1/-2
DSC (Melt Point)	220 / *	°C	ISO 11357
Rheological Properties			
Melt Index (MVR)	55 / *	cm ³ /10min	ISO 1133
MVR temperature	275 / *	°C	-
MVR load	5 / *	kg	-
Shrinkage (lengthwise, 24h)	0.2 - 0.4	%	ISO 294-4
Shrinkage (lateral, 24h)	0.6 - 0.8	%	ISO 294-4
Physical Properties			
Density	1370 / -	kg/m ³	ISO 1183
Flammability			
Flammability (1.5 mm)	HB / *	class	UL 94



ALCOM PA6 900/8.4 GF10 MR20 BK0002-00

(Last update: 30.01.2025)



Liability Exclusion

These are guide values and not a specification. The test values mentioned are representative values only and not binding minimum or maximum figures. These test values have been determined on standardised test specimens and can be affected by pigmentation, mould design and processing conditions.

Any information given on the chemical and physical characteristics of our products, including, without limitation, technical advice on applications, whether verbally, in writing or by testing the product, is given to the best of our knowledge and in good faith and does not exempt the buyer from carrying out their own investigations and tests in order to ascertain the product's specific suitability for the purpose intended.

The buyer is solely responsible for confirming the suitability of the product for a particular application, its utilization and processing and must observe any applicable laws and government regulations. **NO EXPRESS OR IMPLIED RECOMMENDATION OR WARRANTY IS GIVEN WITH REGARD TO THE SUITABILITY OF THE PRODUCT FOR A PARTICULAR APPLICATION, SUCH AS, BUT NOT LIMITED TO, SAFETY-CRITICAL COMPONENTS OR SYSTEMS.**

Healthcare uses: the supply of any product by ALBIS for any medical, pharmaceutical or diagnostic application is conditional to an assessment by ALBIS in terms of compliance with ALBIS' internal risk management policy – even for products which are in general designated for use in Healthcare applications.

Important: irrespective of product type or designation, ALBIS does not recommend or support the use of any products it supplies which fall into the following medical, pharmaceutical or diagnostic application categories:

- risk class III applications according to EU directive 93/42/EEC
- any bodily implant application for greater than 30 days
- any critical component in any medical device that supports or sustains human life.

At all times, our standard terms and conditions of sale apply.