

Bayblend® FR3008 HR (PC+ABS) FR(40)

Covestro Deutschland AG

- (PC ABS)-Blend
- flame retardant
- Vicat/B 120 temperature = 103 °C
- very good hydrolysis resistance compared to a general purpose PC ABS-FR
- e.g. Bayblend FR3010
- HDT/A >= 85 °C
- UL recognition 94 V-0 at 1.5 mm
- Glow wire test: 960 °C at 2.0 mm
- good light stability

Rheological properties	Value	Unit	Test Standard
ISO Data			
Melt volume-flow rate, MVR	13	cm ³ /10min	ISO 1133
Temperature	240	°C	-
Load	5	kg	-

Mechanical Properties	Value	Unit	Test Standard
ISO Data			
Tensile Modulus	2700	MPa	ISO 527
Yield stress	60	MPa	ISO 527
Yield strain	4	%	ISO 527

Thermal Properties	Value	Unit	Test Standard
ISO Data			
Temp. of deflection under load (1.80 MPa)	85	°C	ISO 75-1/-2
Temp. of deflection under load (0.45 MPa)	95	°C	ISO 75-1/-2
Vicat softening temperature, 50°C/h 50N	101	°C	ISO 306
Coeff. of Linear Therm. Expansion, parallel	76	E-6/K	ISO 11359-1/-2
Coeff. of Linear Therm. Expansion, normal	80	E-6/K	ISO 11359-1/-2
Burning Behav. at 1.5 mm Nom. Thickn.	V-0	class	UL 94
Thickness tested	1.5	mm	-
Burning Behav. 5V at Thickness h	5VB	class	IEC 60695-11-20
Thickness tested	2.0	mm	-

Electrical Properties	Value	Unit	Test Standard
ISO Data			
Relative permittivity, 100Hz	3.2	-	IEC 62631-2-1
Relative permittivity, 1MHz	3.1	-	IEC 62631-2-1
Dissipation Factor, 100Hz	50	E-4	IEC 62631-2-1
Dissipation Factor, 1MHz	70	E-4	IEC 62631-2-1
Volume Resistivity	>1E13	Ohm*m	IEC 62631-3-1
Surface Resistivity	>1E15	Ohm	IEC 62631-3-2
Electric Strength	30	kV/mm	IEC 60243-1
Comparative tracking index	300	-	IEC 60112

Other Properties	Value	Unit	Test Standard
ISO Data			
Water Absorption	0.5	%	Sim. to ISO 62
Humidity absorption	0.2	%	Sim. to ISO 62
Density	1200	kg/m ³	ISO 1183


Test specimen production	Value	Unit	Test Standard
ISO Data			
Injection Molding, melt temperature	240	°C	ISO 294
Injection Molding, mold temperature	80	°C	ISO 294
Injection Molding, injection velocity	240	mm/s	ISO 294

Processing Recommendation Injection Molding	Value	Unit	Test Standard
Pre-drying - Temperature	75 - 100	°C	-
Pre-drying - Time	2 - 4	h	-
Processing humidity	≤0.02	%	-


Melt temperature	240 - 280	°C	-
Mold temperature	70 - 100	°C	-

Diagrams

Viscosity-shear rate



Shearstress-shear rate



Characteristics

Processing

Injection Molding

Delivery form

Pellets

Additives

Release agent

Special Characteristics

Flame retardant

Injection Molding

PREPROCESSING

Max. Water content: 0.02 %

Drying temperature: 75 - 100 °C

(depending on the grade 10 °C below the Vicat VST/B120 temperature, but not higher as the recommended values).

Drying time:

Circulating air drying oven (50 % fresh air) 4-8 h

Fresh air dryer (high speed dryer) 2-4 h

Dry air dryer 2-4 h

PROCESSING

Melt temperature: 240-280 °C

Mold temperature: 70-100 °C

Use open nozzle.

Disclaimer

Liability Exclusion

These guide values are measured and provided by the product manufacturer and have been determined on standardised test specimens and can be affected by pigmentation, mould design and processing conditions. M-Base has taken the guide values from the producer's original Technical Data Sheet. **ALBIS AND M-BASE ARE THEREFORE NOT RESPONSIBLE FOR THE ACCURACY OF THE GUIDE VALUES AND CANNOT GIVE ANY WARRANTY WITH REGARD TO THEIR CORRECTNESS.**

Any information given on the chemical and physical characteristics of our products, including, without limitation, technical advice on applications, whether verbally, in writing or by testing the product, is given to the best of our knowledge and in good faith and does not exempt the buyer from carrying out their own investigations and tests in order to ascertain the product's specific suitability for the purpose intended.

The buyer is solely responsible for confirming the suitability of the product for a particular application, its utilization and processing and must observe any applicable laws and government regulations. **NO EXPRESS OR IMPLIED RECOMMENDATION OR WARRANTY IS GIVEN WITH REGARD TO THE SUITABILITY OF THE PRODUCT FOR A PARTICULAR APPLICATION, SUCH AS, BUT NOT LIMITED TO, SAFETY-CRITICAL COMPONENTS OR SYSTEMS.**

Healthcare uses: the supply of any product by ALBIS for any medical, pharmaceutical or diagnostic application is conditional to an assessment by ALBIS in terms of compliance with ALBIS' internal risk management policy – even for products which are in general designated for use in Healthcare applications.

Important: irrespective of product type or designation, ALBIS does not recommend or support the use of any products it supplies which fall into the following medical, pharmaceutical or diagnostic application categories:

- risk class III applications according to EU directive 93/42/EEC
- any bodily implant application for greater than 30 days
- any critical component in any medical device that supports or sustains human life.

At all times, our standard terms and conditions of sale apply.