

Durethan® BKV30PH2.0 901510
PA6-GF30

Envalior


Injection Molding, 30% Glass Reinforced, Heat Stabilized

ISO 1043 PA6-GF30


Rheological properties	dry / cond	Unit	Test Standard
ISO Data			
Molding shrinkage, parallel	0.2 / *	%	ISO 294-4, 2577
Molding shrinkage, normal	0.7 / *	%	ISO 294-4, 2577
Mechanical Properties			
ISO Data			
Tensile Modulus	10000 / 5800	MPa	ISO 527
Stress at Break	170 / 100	MPa	ISO 527
Strain at Break	3.5 / 9	%	ISO 527
Impact Strength (Charpy), +23°C	80 / 100	kJ/m ²	ISO 179/1eU
Impact Strength (Charpy), -30°C	65 / 65	kJ/m ²	ISO 179/1eU
Notched Impact Strength (Charpy), +23°C	10 / 20	kJ/m ²	ISO 179/1eA
Notched Impact Strength (Charpy), -30°C	- / 10	kJ/m ²	ISO 179/1eA
Flexural Modulus (23°C)	9500 / 5600	MPa	ISO 178
Flexural strength	270 / 165	MPa	ISO 178
Notched Impact Strength (Izod), 23°C	15 / 20	kJ/m ²	ISO 180/1A
Notched Impact Strength (Izod)	10 / 10	kJ/m ²	ISO 180/1A
Temperature	-30	°C	-
Impact Strength (Izod), 23°C	70 / 85	kJ/m ²	ISO 180/1U
Thermal Properties			
ISO Data			
Melting Temperature (10°C/min)	220 / *	°C	ISO 11357-1/-3
Temp. of deflection under load (1.80 MPa)	205 / *	°C	ISO 75-1/-2
Temp. of deflection under load (0.45 MPa)	220 / *	°C	ISO 75-1/-2
Coeff. of Linear Therm. Expansion, parallel	20 / *	E-6/K	ISO 11359-1/-2
Coeff. of Linear Therm. Expansion, normal	100 / *	E-6/K	ISO 11359-1/-2
Other Properties			
ISO Data			
Water Absorption	7 / *	%	Sim. to ISO 62
Humidity absorption	2.1 / *	%	Sim. to ISO 62
Density	1360 / -	kg/m ³	ISO 1183
Test specimen production			
ISO Data			
Injection Molding, melt temperature	280	°C	ISO 294
Injection Molding, mold temperature	80	°C	ISO 294
Processing Recommendation Injection Molding			
Pre-drying - Temperature	80	°C	-
Pre-drying - Time	2 - 6	h	-
Processing humidity	≤0.12	%	-
Melt temperature	270 - 290	°C	-
Mold temperature	80 - 120	°C	-

Diagrams


Stress-strain




Stress-strain




Secant modulus-strain




Secant modulus-strain




Stress-strain (isochronous) 23°C




Creep modulus-time 23°C




Stress-strain (isochronous) 90°C




Creep modulus-time 90°C



Stress-strain (isochronous) 120 °C



Creep modulus-time 120 °C



Characteristics

Processing

Injection Molding

Delivery form

Pellets

Special Characteristics

Heat aging stabilized

Features

Fatigue Resistance, Thermal Stability

Applications

Automotive

Injection Molding

PREPROCESSING

Residual moisture content: 0.03 - 0.12%

Drying temperature dry air dryer: 80 °C

Drying time dry air dryer 2 - 6 h

PROCESSING

Melt temperature (Tmin - Tmax): 270 - 290 °C

Mold temperature: 80 - 120 °C

Disclaimer

Liability Exclusion

These guide values are measured and provided by the product manufacturer and have been determined on standardised test specimens and can be affected by pigmentation, mould design and processing conditions. M-Base has taken the guide values from the producer's original Technical Data Sheet. **ALBIS AND M-BASE ARE THEREFORE NOT RESPONSIBLE FOR THE ACCURACY OF THE GUIDE VALUES AND CANNOT GIVE ANY WARRANTY WITH REGARD TO THEIR CORRECTNESS.**

Any information given on the chemical and physical characteristics of our products, including, without limitation, technical advice on applications, whether verbally, in writing or by testing the product, is given to the best of our knowledge and in good faith and does not exempt the buyer from carrying out their own investigations and tests in order to ascertain the product's specific suitability for the purpose intended.

The buyer is solely responsible for confirming the suitability of the product for a particular application, its utilization and processing and must observe any applicable laws and government regulations. **NO EXPRESS OR IMPLIED RECOMMENDATION OR WARRANTY IS GIVEN WITH REGARD TO THE SUITABILITY OF THE PRODUCT FOR A PARTICULAR APPLICATION, SUCH AS, BUT NOT LIMITED TO, SAFETY-CRITICAL COMPONENTS OR SYSTEMS.**

Healthcare uses: the supply of any product by ALBIS for any medical, pharmaceutical or diagnostic application is conditional to an assessment by ALBIS in terms of compliance with ALBIS' internal risk management policy – even for products which are in general designated for use in Healthcare applications.

Important: irrespective of product type or designation, ALBIS does not recommend or support the use of any products it supplies which fall into the following medical, pharmaceutical or

diagnostic application categories:

- risk class III applications according to EU directive 93/42/EEC
- any bodily implant application for greater than 30 days
- any critical component in any medical device that supports or sustains human life.

At all times, our standard terms and conditions of sale apply.