

Pocan® TS3221 901510
 (PBT+PET)-I-GF20

Envalior

Injection Molding, 20% Glass Reinforced, UV Stabilized, Improved Impact, Excellent Surface Properties, Low Warpage

ISO 1043 (PBT+PET)-I-GF20

Rheological properties	Value	Unit	Test Standard
ISO Data			
Melt volume-flow rate, MVR	18	cm³/10min	ISO 1133
Temperature	270	°C	-
Load	5	kg	-
Molding shrinkage, parallel	0.4	%	ISO 294-4, 2577
Molding shrinkage, normal	0.7	%	ISO 294-4, 2577

Mechanical Properties	Value	Unit	Test Standard
ISO Data			
Tensile Modulus	5500	MPa	ISO 527
Stress at Break	75	MPa	ISO 527
Strain at Break	3.3	%	ISO 527
Impact Strength (Charpy), +23°C	50	kJ/m²	ISO 179/1eU
Impact Strength (Charpy), -30°C	45	kJ/m²	ISO 179/1eU
Notched Impact Strength (Charpy), +23°C	10	kJ/m²	ISO 179/1eA
Notched Impact Strength (Charpy), -30°C	10	kJ/m²	ISO 179/1eA

Thermal Properties	Value	Unit	Test Standard
ISO Data			
Temp. of deflection under load (1.80 MPa)	140	°C	ISO 75-1/-2
Temp. of deflection under load (0.45 MPa)	205	°C	ISO 75-1/-2
Coeff. of Linear Therm. Expansion, parallel	30	E-6/K	ISO 11359-1/-2
Coeff. of Linear Therm. Expansion, normal	130	E-6/K	ISO 11359-1/-2

Electrical Properties	Value	Unit	Test Standard
ISO Data			
Comparative tracking index	250	-	IEC 60112


Other Properties	Value	Unit	Test Standard
ISO Data			
Density	1390	kg/m³	ISO 1183

Test specimen production	Value	Unit	Test Standard
ISO Data			
Injection Molding, melt temperature	270	°C	ISO 294
Injection Molding, mold temperature	90	°C	ISO 294


Processing Recommendation Injection Molding	Value	Unit	Test Standard
Pre-drying - Temperature	120	°C	-
Pre-drying - Time	4 - 8	h	-
Processing humidity	≤0.02	%	-
Melt temperature	260 - 280	°C	-
Mold temperature	80 - 100	°C	-

Diagrams

Stress-strain



Secant modulus-strain



Characteristics

Processing

Injection Molding, Calendering

Delivery form

Pellets

Special Characteristics

Impact modified, UV stabilized, Heat aging stabilized

Features

Low Warpage

Injection Molding

PREPROCESSING

Residual moisture content: 0.00 - 0.02 %

Drying temperature circulating air dryer: 120 °C

Drying time circulating air dryer: 4 - 8 h

PROCESSING

Melt temperature (Tmin - Tmax): 260 - 280 °C

Mold temperature: 80 - 100 °C

Disclaimer

Liability Exclusion

These guide values are measured and provided by the product manufacturer and have been determined on standardised test specimens and can be affected by pigmentation, mould design and processing conditions. M-Base has taken the guide values from the producer's original Technical Data Sheet. **ALBIS AND M-BASE ARE THEREFORE NOT RESPONSIBLE FOR THE ACCURACY OF THE GUIDE VALUES AND CANNOT GIVE ANY WARRANTY WITH REGARD TO THEIR CORRECTNESS.**

Any information given on the chemical and physical characteristics of our products, including, without limitation, technical advice on applications, whether verbally, in writing or by testing the product, is given to the best of our knowledge and in good faith and does not exempt the buyer from carrying out their own investigations and tests in order to ascertain the product's specific suitability for the purpose intended.

The buyer is solely responsible for confirming the suitability of the product for a particular application, its utilization and processing and must observe any applicable laws and government regulations. **NO EXPRESS OR IMPLIED RECOMMENDATION OR WARRANTY IS GIVEN WITH REGARD TO THE SUITABILITY OF THE PRODUCT FOR A PARTICULAR APPLICATION, SUCH AS, BUT NOT LIMITED TO, SAFETY-CRITICAL COMPONENTS OR SYSTEMS.**

Healthcare uses: the supply of any product by ALBIS for any medical, pharmaceutical or diagnostic application is conditional to an assessment by ALBIS in terms of compliance with ALBIS' internal risk management policy – even for products which are in general designated for use in Healthcare applications.

Important: irrespective of product type or designation, ALBIS does not recommend or support the use of any products it supplies which fall into the following medical, pharmaceutical or diagnostic application categories:

- risk class III applications according to EU directive 93/42/EEC
- any bodily implant application for greater than 30 days
- any critical component in any medical device that supports or sustains human life.

At all times, our standard terms and conditions of sale apply.