

Ultraform® N2200 G43 AT
POM-GF20

BASF

Injection molding grade for parts requiring high stiffness and strength together with good mold release.

Abbreviated designation according to ISO 1043: POM-GF20
Designation according to ISO 29988-POM-K,GF20,M-GNR,2-3

Rheological properties	Value	Unit	Test Standard
ISO Data			
Melt volume-flow rate, MVR	3.5	cm³/10min	ISO 1133
Temperature	190	°C	-
Load	2.16	kg	-
Molding shrinkage, parallel	0.7	%	ISO 294-4, 2577
Molding shrinkage, normal	1.1	%	ISO 294-4, 2577

Mechanical Properties	Value	Unit	Test Standard
ISO Data			
Tensile Modulus	7800	MPa	ISO 527
Stress at Break	120	MPa	ISO 527
Strain at Break	2.7	%	ISO 527
Impact Strength (Charpy), +23°C	50	kJ/m²	ISO 179/1eU
Impact Strength (Charpy), -30°C	50	kJ/m²	ISO 179/1eU
Notched Impact Strength (Charpy), +23°C	7.5	kJ/m²	ISO 179/1eA
Notched Impact Strength (Charpy), -30°C	7.5	kJ/m²	ISO 179/1eA

Thermal Properties	Value	Unit	Test Standard
ISO Data			
Melting Temperature (10°C/min)	165	°C	ISO 11357-1/-3
Temp. of deflection under load (1.80 MPa)	161	°C	ISO 75-1/-2
Vicat softening temperature, 50°C/h 50N	160	°C	ISO 306
Coeff. of Linear Therm. Expansion, parallel	50	E-6/K	ISO 11359-1/-2
Burning Behav. at 1.5 mm Nom. Thickn.	HB	class	UL 94
Thickness tested	1.6	mm	-
UL recognition	yes	-	-
Burning Behav. at thickness h	HB	class	UL 94
Thickness tested	0.8	mm	-

Electrical Properties	Value	Unit	Test Standard
ISO Data			
Relative permittivity, 100Hz	4	-	IEC 62631-2-1
Relative permittivity, 1MHz	4.1	-	IEC 62631-2-1
Dissipation Factor, 100Hz	40	E-4	IEC 62631-2-1
Dissipation Factor, 1MHz	70	E-4	IEC 62631-2-1
Volume Resistivity	1E10	Ohm*m	IEC 62631-3-1
Surface Resistivity	1E14	Ohm	IEC 62631-3-2
Electric Strength	43	kV/mm	IEC 60243-1
Comparative tracking index	600	-	IEC 60112

Other Properties	Value	Unit	Test Standard
ISO Data			
Water Absorption	1	%	Sim. to ISO 62
Humidity absorption	0.2	%	Sim. to ISO 62
Density	1550	kg/m³	ISO 1183

Rheological calculation properties	Value	Unit	Test Standard
ISO Data			
Density of melt	1330	kg/m³	-
Thermal Conductivity of Melt	0.2	W/(m K)	-
Ejection temperature	125	°C	-

Test specimen production	Value	Unit	Test Standard
ISO Data			
Injection Molding, melt temperature	200	°C	ISO 294

Injection Molding, mold temperature	90	°C	ISO 294
Injection Molding, injection velocity	200	mm/s	ISO 294

Processing Recommendation Injection Molding	Value	Unit	Test Standard
Pre-drying - Temperature	100	°C	-
Pre-drying - Time	3	h	-
Processing humidity	≤0.2	%	-
Melt temperature	190 - 220	°C	-
Mold temperature	60 - 120	°C	-

Characteristics

Processing

Injection Molding

Additives

Release agent

Delivery form

Pellets

Features

Copolymer

Injection Molding

PREPROCESSING

Pre/Post-processing, max. allowed water content: .2 %

Pre/Post-processing, Pre-drying, Temperature: 100 °C

Pre/Post-processing, Pre-drying, Time: 3 h

PROCESSING

injection molding, Melt temperature, range: 190 - 220 °C

injection molding, Melt temperature, recommended: 210 °C

injection molding, Mold temperature, range: 60 - 120 °C

injection molding, Mold temperature, recommended: 100 °C

injection molding, Dwell time, thermoplastics: 10 min

Processing

Usual single-flighted three-section screws with an effective screw length of at least 15 D, better 20 - 23 D are suitable for the injection molding of Ultraform.

Pretreatment

Granules or pellets in original packaging can be processed without any special pretreatment. Granules or pellets which have become moist due to prolonged or incorrect storage (e.g. by formation of condensed water) must be dried in dehumidifying or recirculating air dryers for approx. 3 hours at about 100 - 110 °C. The moisture content should not exceed 0.2 %.

Postprocessing

If parts were produced at a comparatively low mold temperature (e.g. in order to obtain short cycle times) and must not change their geometry in use thermal postprocessing inducing dimensional changes by postcrystallization may be necessary. In such cases parts should be stored in an oven with recirculated air at temperatures of 100 - 130 °C until dimensions don't change significantly any further. The time needed for this has to be determined experimentally.

Disclaimer

Liability Exclusion

These guide values are measured and provided by the product manufacturer and have been determined on standardised test specimens and can be affected by pigmentation, mould design and processing conditions. M-Base has taken the guide values from the producer's original Technical Data Sheet. **ALBIS AND M-BASE ARE THEREFORE NOT RESPONSIBLE FOR THE ACCURACY OF THE GUIDE VALUES AND CANNOT GIVE ANY WARRANTY WITH REGARD TO THEIR CORRECTNESS.**

Any information given on the chemical and physical characteristics of our products, including, without limitation, technical advice on applications, whether verbally, in writing or by testing the product, is given to the best of our knowledge and in good faith and does not exempt the buyer from carrying out their own investigations and tests in order to ascertain the product's specific suitability for the purpose intended.

The buyer is solely responsible for confirming the suitability of the product for a particular application, its utilization and processing and must observe any applicable laws and government regulations. **NO EXPRESS OR IMPLIED RECOMMENDATION OR WARRANTY IS GIVEN WITH REGARD TO THE SUITABILITY OF THE PRODUCT FOR A PARTICULAR APPLICATION, SUCH AS, BUT NOT LIMITED TO, SAFETY-CRITICAL COMPONENTS OR SYSTEMS.**

Healthcare uses: the supply of any product by ALBIS for any medical, pharmaceutical or diagnostic application is conditional to an assessment by ALBIS in terms of compliance with ALBIS' internal risk management policy – even for products which are in general designated for use in Healthcare applications.

Important: irrespective of product type or designation, ALBIS does not recommend or support the use of any products it supplies which fall into the following medical, pharmaceutical or diagnostic application categories:

- risk class III applications according to EU directive 93/42/EEC
- any bodily implant application for greater than 30 days
- any critical component in any medical device that supports or sustains human life.

At all times, our standard terms and conditions of sale apply.