

Ultraform® S1320 003 AT
POM

BASF

Free-flowing, rapidly solidifying grade for moldings difficult to produce by injection molding and having low wall thickness; increased stiffness and heat distortion resistance.

Abbreviated designation according to ISO 1043-1: POM
Designation according to ISO 29988-POM-K,,M-GNR,4-2

Rheological properties	Value	Unit	Test Standard
ISO Data			
Melt volume-flow rate, MVR	11	cm³/10min	ISO 1133
Temperature	190	°C	-
Load	2.16	kg	-
Molding shrinkage, parallel	2.1	%	ISO 294-4, 2577
Molding shrinkage, normal	2.1	%	ISO 294-4, 2577

Mechanical Properties	Value	Unit	Test Standard
ISO Data			
Tensile Modulus	3000	MPa	ISO 527
Yield stress	67	MPa	ISO 527
Yield strain	10.5	%	ISO 527
Nominal strain at break	25	%	ISO 527
Tensile Creep Modulus, 1000h	1450	MPa	ISO 899-1
Impact Strength (Charpy), +23°C	230	kJ/m²	ISO 179/1eU
Impact Strength (Charpy), -30°C	210	kJ/m²	ISO 179/1eU
Notched Impact Strength (Charpy), +23°C	6	kJ/m²	ISO 179/1eA
Notched Impact Strength (Charpy), -30°C	5.5	kJ/m²	ISO 179/1eA

Thermal Properties	Value	Unit	Test Standard
ISO Data			
Melting Temperature (10°C/min)	170	°C	ISO 11357-1/-3
Temp. of deflection under load (1.80 MPa)	100	°C	ISO 75-1/-2
Temp. of deflection under load (0.45 MPa)	159	°C	ISO 75-1/-2
Vicat softening temperature, 50°C/h 50N	150	°C	ISO 306
Coeff. of Linear Therm. Expansion, parallel	110	E-6/K	ISO 11359-1/-2
Burning Behav. at 1.5 mm Nom. Thickn.	HB	class	UL 94
Thickness tested	1.6	mm	-
UL recognition	yes	-	-
Burning Behav. at thickness h	HB	class	UL 94
Thickness tested	0.8	mm	-
UL recognition	yes	-	-
Oxygen index	15	%	ISO 4589-1/-2

Electrical Properties	Value	Unit	Test Standard
ISO Data			
Relative permittivity, 100Hz	3.7	-	IEC 62631-2-1
Relative permittivity, 1MHz	3.7	-	IEC 62631-2-1
Dissipation Factor, 100Hz	20	E-4	IEC 62631-2-1
Dissipation Factor, 1MHz	50	E-4	IEC 62631-2-1
Volume Resistivity	1E11	Ohm*m	IEC 62631-3-1
Surface Resistivity	1E15	Ohm	IEC 62631-3-2
Electric Strength	40	kV/mm	IEC 60243-1
Comparative tracking index	600	-	IEC 60112

Other Properties	Value	Unit	Test Standard
ISO Data			
Water Absorption	0.9	%	Sim. to ISO 62
Humidity absorption	0.2	%	Sim. to ISO 62
Density	1410	kg/m³	ISO 1183


Rheological calculation properties	Value	Unit	Test Standard
ISO Data			
Ejection temperature	110	°C	-

Test specimen production	Value	Unit	Test Standard
ISO Data			
Injection Molding, melt temperature	200	°C	ISO 294
Injection Molding, mold temperature	90	°C	ISO 294
Injection Molding, injection velocity	200	mm/s	ISO 294

Processing Recommendation Injection Molding	Value	Unit	Test Standard
Pre-drying - Temperature	100	°C	-
Pre-drying - Time	3	h	-
Processing humidity	≤0.2	%	-
Melt temperature	190 - 230	°C	-
Mold temperature	60 - 120	°C	-

Diagrams

Specific volume-temperature (pvT)



Characteristics

Processing

Injection Molding

Delivery form

Pellets

Additives

Release agent

Injection Molding

PREPROCESSING

Pre/Post-processing, max. allowed water content: .2 %

Pre/Post-processing, Pre-drying, Temperature: 100 °C

Pre/Post-processing, Pre-drying, Time: 3 h

PROCESSING

injection molding, Melt temperature, range: 190 - 230 °C

injection molding, Melt temperature, recommended: 200 °C

injection molding, Mold temperature, range: 60 - 120 °C

injection molding, Mold temperature, recommended: 90 °C

injection molding, Dwell time, thermoplastics: 10 min

Processing

Usual single-flighted three-section screws with an effective screw length of at least 15 D, better 20 - 23 D are suitable for the injection molding

of Ultraform.

Pretreatment

Granules or pellets in original packaging can be processed without any special pretreatment. Granules or pellets which have become moist due to prolonged or incorrect storage (e.g. by formation of condensed water) must be dried in dehumidifying or recirculating air dryers for approx. 3 hours at about 100 - 110 °C. The moisture content should not exceed 0.2 %.

Postprocessing

If parts were produced at a comparatively low mold temperature (e.g. in order to obtain short cycle times) and must not change their geometry in use thermal postprocessing inducing dimensional changes by postcrystallization may be necessary. In such cases parts should be stored in an oven with recirculated air at temperatures of 100 - 130 °C until dimensions don't change significantly any further. The time needed for this has to be determined experimentally.

Disclaimer

Liability Exclusion

These guide values are measured and provided by the product manufacturer and have been determined on standardised test specimens and can be affected by pigmentation, mould design and processing conditions. M-Base has taken the guide values from the producer's original Technical Data Sheet. **ALBIS AND M-BASE ARE THEREFORE NOT RESPONSIBLE FOR THE ACCURACY OF THE GUIDE VALUES AND CANNOT GIVE ANY WARRANTY WITH REGARD TO THEIR CORRECTNESS.**

Any information given on the chemical and physical characteristics of our products, including, without limitation, technical advice on applications, whether verbally, in writing or by testing the product, is given to the best of our knowledge and in good faith and does not exempt the buyer from carrying out their own investigations and tests in order to ascertain the product's specific suitability for the purpose intended.

The buyer is solely responsible for confirming the suitability of the product for a particular application, its utilization and processing and must observe any applicable laws and government regulations. **NO EXPRESS OR IMPLIED RECOMMENDATION OR WARRANTY IS GIVEN WITH REGARD TO THE SUITABILITY OF THE PRODUCT FOR A PARTICULAR APPLICATION, SUCH AS, BUT NOT LIMITED TO, SAFETY-CRITICAL COMPONENTS OR SYSTEMS.**

Healthcare uses: the supply of any product by ALBIS for any medical, pharmaceutical or diagnostic application is conditional to an assessment by ALBIS in terms of compliance with ALBIS' internal risk management policy – even for products which are in general designated for use in Healthcare applications.

Important: irrespective of product type or designation, ALBIS does not recommend or support the use of any products it supplies which fall into the following medical, pharmaceutical or diagnostic application categories:

- risk class III applications according to EU directive 93/42/EEC
- any bodily implant application for greater than 30 days
- any critical component in any medical device that supports or sustains human life.

At all times, our standard terms and conditions of sale apply.