

Ultramid® B3Z2

PA6-I

BASF

Injection moulding grade, easy flowing, short cycle time, dry-impact, conditioning free technical moulded parts

Rheological properties	dry / cond	Unit	Test Standard
ISO Data			
Melt volume-flow rate, MVR	100 / *	cm³/10min	ISO 1133
Temperature	275 / *	°C	-
Load	5 / *	kg	-
Molding shrinkage, parallel	1.3 / *	%	ISO 294-4, 2577
Molding shrinkage, normal	1.4 / *	%	ISO 294-4, 2577

Mechanical Properties	dry / cond	Unit	Test Standard
ISO Data			
Tensile Modulus	2090 / 650	MPa	ISO 527
Yield stress	57 / 30	MPa	ISO 527
Yield strain	4 / 20	%	ISO 527
Nominal strain at break	50 / >50	%	ISO 527
Impact Strength (Charpy), +23°C	no break / no break	kJ/m²	ISO 179/1eU
Impact Strength (Charpy), -30°C	no break / -	kJ/m²	ISO 179/1eU
Notched Impact Strength (Charpy), +23°C	56 / 128	kJ/m²	ISO 179/1eA
Notched Impact Strength (Charpy), -30°C	20 / -	kJ/m²	ISO 179/1eA
Flexural Modulus (23°C)	1800 / -	MPa	ISO 178

Thermal Properties	dry / cond	Unit	Test Standard
ISO Data			
Melting Temperature (10°C/min)	220 / *	°C	ISO 11357-1/-3
Temp. of deflection under load (1.80 MPa)	60 / *	°C	ISO 75-1/-2

Electrical Properties	dry / cond	Unit	Test Standard
ISO Data			
Relative permittivity, 1MHz	3.4 / -	-	IEC 62631-2-1
Dissipation Factor, 1MHz	150 / -	E-4	IEC 62631-2-1
Volume Resistivity	>1E13 / -	Ohm*m	IEC 62631-3-1

Other Properties	dry / cond	Unit	Test Standard
ISO Data			
Water Absorption	8.5 / *	%	Sim. to ISO 62
Humidity absorption	2.8 / *	%	Sim. to ISO 62
Density	1090 / -	kg/m³	ISO 1183
Bulk density	700	kg/m³	-

Test specimen production	Value	Unit	Test Standard
ISO Data			
Processing conditions acc. ISO	1874	-	ISO-2
Injection Molding, melt temperature	240	°C	ISO 294
Injection Molding, mold temperature	80	°C	ISO 294
Injection Molding, injection velocity	200	mm/s	ISO 294

Processing Recommendation Injection Molding	Value	Unit	Test Standard
Pre-drying - Temperature	80	°C	-
Pre-drying - Time	4	h	-
Processing humidity	≤0.15	%	-
Melt temperature	250 - 270	°C	-
Mold temperature	40 - 60	°C	-

Characteristics

Processing

Injection Molding

Special Characteristics

Impact modified

Delivery form

Pellets

Applications

Automotive

Additives

Release agent

Injection Molding

PREPROCESSING

Pre/Post-processing, max. allowed water content: .15 %

Pre/Post-processing, Pre-drying, Temperature: 80 °C

Pre/Post-processing, Pre-drying, Time: 4 h

PROCESSING

injection molding, Melt temperature, range: 250 - 270 °C

injection molding, Melt temperature, recommended: 260 °C

injection molding, Mold temperature, range: 40 - 60 °C

injection molding, Mold temperature, recommended: 60 °C

injection molding, Dwell time, thermoplastics: 10 min

Chemical Media Resistance

Acids

✓ Acetic Acid (5% by mass) (23°C)

Disclaimer

Liability Exclusion

These guide values are measured and provided by the product manufacturer and have been determined on standardised test specimens and can be affected by pigmentation, mould design and processing conditions. M-Base has taken the guide values from the producer's original Technical Data Sheet. **ALBIS AND M-BASE ARE THEREFORE NOT RESPONSIBLE FOR THE ACCURACY OF THE GUIDE VALUES AND CANNOT GIVE ANY WARRANTY WITH REGARD TO THEIR CORRECTNESS.**

Any information given on the chemical and physical characteristics of our products, including, without limitation, technical advice on applications, whether verbally, in writing or by testing the product, is given to the best of our knowledge and in good faith and does not exempt the buyer from carrying out their own investigations and tests in order to ascertain the product's specific suitability for the purpose intended.

The buyer is solely responsible for confirming the suitability of the product for a particular application, its utilization and processing and must observe any applicable laws and government regulations. **NO EXPRESS OR IMPLIED RECOMMENDATION OR WARRANTY IS GIVEN WITH REGARD TO THE SUITABILITY OF THE PRODUCT FOR A PARTICULAR APPLICATION, SUCH AS, BUT NOT LIMITED TO, SAFETY-CRITICAL COMPONENTS OR SYSTEMS.**

Healthcare uses: the supply of any product by ALBIS for any medical, pharmaceutical or diagnostic application is conditional to an assessment by ALBIS in terms of compliance with ALBIS' internal risk management policy – even for products which are in general designated for use in Healthcare applications.

Important: irrespective of product type or designation, ALBIS does not recommend or support the use of any products it supplies which fall into the following medical, pharmaceutical or diagnostic application categories:

- risk class III applications according to EU directive 93/42/EEC
- any bodily implant application for greater than 30 days
- any critical component in any medical device that supports or sustains human life.

At all times, our standard terms and conditions of sale apply.