

Ultrason® E 2010 C6
PESU-CF30

BASF

Medium viscosity injection moulding grade with high rigidity and strength, 30 % carbon fiber reinforced.
Abbreviated designation according to ISO 1043: PESU-CF

Rheological properties	dry / cond	Unit	Test Standard
ISO Data			
Melt volume-flow rate, MVR	15 / *	cm³/10min	ISO 1133
Temperature	360 / *	°C	-
Load	10 / *	kg	-
Molding shrinkage, parallel	0.1 / *	%	ISO 294-4, 2577
Molding shrinkage, normal	0.3 / *	%	ISO 294-4, 2577

Mechanical Properties	dry / cond	Unit	Test Standard
ISO Data			
Tensile Modulus	- / 21200	MPa	ISO 527
Stress at Break	- / 180	MPa	ISO 527
Strain at Break	- / 1.4	%	ISO 527
Impact Strength (Charpy), +23°C	- / 39	kJ/m²	ISO 179/1eU
Impact Strength (Charpy), -30°C	- / 39	kJ/m²	ISO 179/1eU
Notched Impact Strength (Charpy), +23°C	- / 7	kJ/m²	ISO 179/1eA
Notched Impact Strength (Charpy), -30°C	- / 6	kJ/m²	ISO 179/1eA

Thermal Properties	dry / cond	Unit	Test Standard
ISO Data			
Glass Transition Temperature (10°C/min)	225 / *	°C	ISO 11357-1/-2
Temp. of deflection under load (1.80 MPa)	225 / *	°C	ISO 75-1/-2
Temp. of deflection under load (0.45 MPa)	230 / *	°C	ISO 75-1/-2
Coeff. of Linear Therm. Expansion, parallel	4 / *	E-6/K	ISO 11359-1/-2
Coeff. of Linear Therm. Expansion, normal	37 / *	E-6/K	ISO 11359-1/-2
Oxygen index	51.9 / *	%	ISO 4589-1/-2

Electrical Properties	dry / cond	Unit	Test Standard
ISO Data			
Surface Resistivity	* / 1000	Ohm	IEC 62631-3-2

Other Properties	dry / cond	Unit	Test Standard
ISO Data			
Water Absorption	1.7 / *	%	Sim. to ISO 62
Humidity absorption	0.6 / *	%	Sim. to ISO 62
Density	1470 / -	kg/m³	ISO 1183


Material Specific Properties	dry / cond	Unit	Test Standard
ISO Data			
Viscosity number	56 / *	cm³/g	ISO 307, 1157, 1628

Test specimen production	Value	Unit	Test Standard
ISO Data			
Injection Molding, melt temperature	370	°C	ISO 294
Injection Molding, mold temperature	170	°C	ISO 294


Processing Recommendation Injection Molding	Value	Unit	Test Standard
Pre-drying - Temperature	140	°C	-
Pre-drying - Time	4	h	-
Processing humidity	≤0.02	%	-
Melt temperature	350 - 390	°C	-
Mold temperature	150 - 190	°C	-

Diagrams


Stress-strain (isochronous) 23 °C



Creep modulus-time 23 °C



Specific volume-temperature (pvT)



Characteristics

Processing

Injection Molding, Profile Extrusion, Sheet Extrusion, Other Extrusion

Delivery form

Pellets

Special Characteristics

Electrically Conductive, Anti-static

Injection Molding

PREPROCESSING

Pre/Post-processing, max. allowed water content: .02 %

Pre/Post-processing, Pre-drying, Temperature: 140 °C

Pre/Post-processing, Pre-drying, Time: 4 h

PROCESSING

injection molding, Melt temperature, range: 350 - 390 °C
injection molding, Melt temperature, recommended: 370 °C
injection molding, Mold temperature, range: 150 - 190 °C
injection molding, Mold temperature, recommended: 170 °C
injection molding, Dwell time, thermoplastics: 10 min

Pretreatment

Drying temperature: 130 - 150 °C
Drying time: minimum 4h
recommended dryer: vacuum or dry air dryer
maximum moisture: 0,02 - 0,05%

Ultrason® can be injection molded by any type of machinery on the market, provided that the plasticizing unit and the mold temperature control system have been configured appropriately. The machinery manufacturer must be consulted if any doubts exist on the ability of various parts to withstand the high temperatures required (e.g. barrel, barrel head, bolted connections, etc.)

Long residence time in combination with high temperatures should be avoided e.g. by pump out material at regular intervals.
During extended interruptions, the barrel temperature should be lowered to about 250-280 °C.

It has been found out that heating to the requested processing temperature and shutting down or lowering the temperature is best carried out in two steps.

First, the barrel temperatures are set at the lower processing temperature range for the particular thermoplastic (340 - 350 °C). As soon as these temperatures have reached a steady state, the material in the barrel is pumped out. Second, the barrel temperature can be set to the required processing temperature or the heaters can be shut down.

Disclaimer

Liability Exclusion

These guide values are measured and provided by the product manufacturer and have been determined on standardised test specimens and can be affected by pigmentation, mould design and processing conditions. M-Base has taken the guide values from the producer's original Technical Data Sheet. **ALBIS AND M-BASE ARE THEREFORE NOT RESPONSIBLE FOR THE ACCURACY OF THE GUIDE VALUES AND CANNOT GIVE ANY WARRANTY WITH REGARD TO THEIR CORRECTNESS.**

Any information given on the chemical and physical characteristics of our products, including, without limitation, technical advice on applications, whether verbally, in writing or by testing the product, is given to the best of our knowledge and in good faith and does not exempt the buyer from carrying out their own investigations and tests in order to ascertain the product's specific suitability for the purpose intended.

The buyer is solely responsible for confirming the suitability of the product for a particular application, its utilization and processing and must observe any applicable laws and government regulations. **NO EXPRESS OR IMPLIED RECOMMENDATION OR WARRANTY IS GIVEN WITH REGARD TO THE SUITABILITY OF THE PRODUCT FOR A PARTICULAR APPLICATION, SUCH AS, BUT NOT LIMITED TO, SAFETY-CRITICAL COMPONENTS OR SYSTEMS.**

Healthcare uses: the supply of any product by ALBIS for any medical, pharmaceutical or diagnostic application is conditional to an assessment by ALBIS in terms of compliance with ALBIS' internal risk management policy – even for products which are in general designated for use in Healthcare applications.

Important: irrespective of product type or designation, ALBIS does not recommend or support the use of any products it supplies which fall into the following medical, pharmaceutical or diagnostic application categories:

- risk class III applications according to EU directive 93/42/EEC
- any bodily implant application for greater than 30 days
- any critical component in any medical device that supports or sustains human life.

At all times, our standard terms and conditions of sale apply.