

!'ALBIS

VESTAKEEP® 4000 GF30 PEEK-GF30

Evonik Operations GmbH

Glass fiber-reinforced (30%) polyether ether ketone

VESTAKEEP® 4000 GF30 is a glass fiber-reinforced (30%) polyether ether ketone for injection molding.

The semi-crystalline polymer features superior mechanical, thermal, and chemical resistance. Parts made from VESTAKEEP® 4000 GF30 are of low flammability.

VESTAKEEP® 4000 GF30 can be processed on common injection molding machines for thermoplastics.

We recommend a melt temperature of 380°C to 400°C during the injection molding process. The mold temperature should be within a range of 160°C to 200°C, preferably 180°C.

VESTAKEEP® 4000 GF30 is supplied as cylindrical pellets in 25kg boxes with moisture-proof polyethylene liners.

Inside the original and undamaged packaging, the product has a shelf life of at least 2 years when stored in dry rooms at temperatures not exceeding 30°C.

Pigmentation may affect the values.

For guidance processing of VESTAKEEP® 4000 GF30 please follow the general recommendations in our brochure "VESTAKEEP® PEEK Processing Guidelines".

The values presented are typical or average values, they do not constitute a specification.

FOR FURTHER INFORMATION PLEASE CONTACT US AT <u>EVONIK-HP@EVONIK.COM</u> OR VISIT OUR PRODUCT AT <u>WWW.INDUSTRIAL.VESTAKEEP.COM</u>

Rheological properties	Value	Unit	Test Standard
ISO Data			
Melt volume-flow rate, MVR	32	cm ³ /10min	ISO 1133
Temperature	400	°C	-
Load	21.6	kg	-
Molding shrinkage, parallel	0.3	%	ISO 294-4, 2577
Molding shrinkage, normal	0.7	%	ISO 294-4, 2577

Mechanical Properties	Value	Unit	Test Standard
ISO Data			
Tensile Modulus	11000	MPa	ISO 527
Stress at Break	160	MPa	ISO 527
Strain at Break	2	%	ISO 527
Impact Strength (Charpy), +23°C	70	kJ/m²	ISO 179/1eU
Type of failure	С	-	-
Impact Strength (Charpy), -30°C	75	kJ/m²	ISO 179/1eU
Type of failure	С	-	-
Notched Impact Strength (Charpy), +23°C	11	kJ/m²	ISO 179/1eA
Type of failure	С	-	-
Notched Impact Strength (Charpy), -30°C	9	kJ/m²	ISO 179/1eA
Type of failure	С	-	-

Thermal Properties	Value	Unit	Test Standard
ISO Data			
Melting Temperature (10°C/min)	340	°C	ISO 11357-1/-3
Temp. of deflection under load (1.80 MPa)	312	°C	ISO 75-1/-2
Temp. of deflection under load (0.45 MPa)	335	°C	ISO 75-1/-2
Vicat softening temperature, 50°C/h 50N	335	°C	ISO 306
Coeff. of Linear Therm. Expansion, parallel	30	E-6/K	ISO 11359-1/-2
Burning Behav. at 1.5 mm Nom. Thickn.	V-0	class	UL 94
Thickness tested	1.6	mm	-
Oxygen index	45	%	ISO 4589-1/-2


Electrical Properties	Value	Unit	Test Standard
ISO Data			
Relative permittivity, 1MHz	3.3	-	IEC 62631-2-1
Dissipation Factor, 1MHz	40	E-4	IEC 62631-2-1
Volume Resistivity	>1E13	Ohm*m	IEC 62631-3-1
Surface Resistivity	1E15	Ohm	IEC 62631-3-2
Comparative tracking index	200	-	IEC 60112

Other Properties	Value	Unit	Test Standard
ISO Data			
Water Absorption	0.4	%	Sim. to ISO 62
Density	1500	kg/m³	ISO 1183

Test specimen production	Value	Unit	Test Standard
ISO Data			
Injection Molding, melt temperature	400	°C	ISO 294
Injection Molding, mold temperature	180	°C	ISO 294
Injection Molding, injection velocity	200	mm/s	ISO 294
Injection Molding, pressure at hold	120	MPa	ISO 294

Diagrams

Tensile Modulus-Temperature



Characteristics

Processing

Injection Molding, Other Extrusion

Delivery form

Pellets

Chemical Media Resistance

Acids

- ✓ Acetic Acid (5% by mass) (23°C)
- ✓ Citric Acid solution (10% by mass) (23°C)
- ✓ Hydrochloric Acid (36% by mass) (23°C)
- X Nitric Acid (40% by mass) (23°C)
- ✓ Sulfuric Acid (5% by mass) (23°C)
- ✓ Chromic Acid solution (40% by mass) (23°C)

Bases

- ✓ Sodium Hydroxide solution (35% by mass) (23°C)
- ✓ Sodium Hydroxide solution (1% by mass) (23°C)
- ✓ Ammonium Hydroxide solution (10% by mass) (23°C)

Alcohols

- ✓ Isopropyl alcohol (23°C)
- ✓ Methanol (23°C)
- ✓ Ethanol (23°C)

Hydrocarbons

- ✓ n-Hexane (23°C)
- ✓ Toluene (23°C)
- ✓ iso-Octane (23°C)

Ketones

✓ Acetone (23°C)

Ethers

✓ Diethyl ether (23°C)

Mineral oils

- ✓ SAE 10W40 multigrade motor oil (23°C)
- ✓ Insulating Oil (23°C)

Standard Fuels

- ✓ Standard fuel without alcohol (pref. ISO 1817 Liquid C) (23°C)
- ✓ Standard fuel with alcohol (pref. ISO 1817 Liquid 4) (23°C)
- ✓ Diesel fuel (pref. ISO 1817 Liquid F) (23°C)

Salt solutions

- ✓ Sodium Chloride solution (10% by mass) (23°C)
- ✓ Sodium Hypochlorite solution (10% by mass) (23°C)
- ✓ Sodium Carbonate solution (20% by mass) (23°C)
- ✓ Sodium Carbonate solution (2% by mass) (23°C)
- ✓ Zinc Chloride solution (50% by mass) (23°C)

Other

- ✓ Ethyl Acetate (23°C)
- ✓ Hydrogen peroxide (23°C)
- ✓ Ethylene Glycol (50% by mass) in water (108°C)
- ✓ Water (23°C)
- ✓ Deionized water (90°C)

Disclaimer

Liability Exclusion

These guide values are measured and provided by the product manufacturer and have been determined on standardised test specimens and can be affected by pigmentation, mould design and processing conditions. M-Base has taken the guide values from the producer's original Technical Data Sheet. ALBIS AND M-BASE ARE THEREFORE NOT RESPONSIBLE FOR THE ACCURACY OF THE GUIDE VALUES AND CANNOT GIVE ANY WARRANTY WITH REGARD TO THEIR CORRECTNESS.

Any information given on the chemical and physical characteristics of our products, including, without limitation, technical advice on applications, whether verbally, in writing or by testing the product, is given to the best of our knowledge and in good faith and does not exempt the buyer from carrying out their own investigations and tests in order to ascertain the product's specific suitability for the purpose intended.

The buyer is solely responsible for confirming the suitability of the product for a particular application, its utilization and processing and must observe any applicable laws and government regulations. NO EXPRESS OR IMPLIED RECOMMENDATION OR WARRANTY IS GIVEN WITH REGARD TO THE SUITABILITY OF THE PRODUCT FOR A PARTICULAR APPLICATION, SUCH AS, BUT NOT LIMITED TO, SAFETY-CRITICAL COMPONENTS OR SYSTEMS.

Healthcare uses: the supply of any product by ALBIS for any medical, pharmaceutical or diagnostic application is conditional to an assessment by ALBIS in terms of compliance with ALBIS' internal risk management policy – even for products which are in general designated for use in Healthcare applications.

Important: irrespective of product type or designation, ALBIS does not recommend or support the use of any products it supplies which fall into the following medical, pharmaceutical or

Important: irrespective of product type or designation, ALBIS does not recommend or support the use of any products it supplies which fall into the following medical, pharmaceutical or diagnostic application categories:

- risk class III applications according to EU directive 93/42/EEC
- any bodily implant application for greater than 30 days
- any critical component in any medical device that supports or sustains human life.

At all times, our standard terms and conditions of sale apply.