DuPont Packaging & Industrial Polymers





DuPont™ Bynel® 22E757

Bynel® resins Product Data Sheet

-					-0		
1	es	^	71	n	71	$\boldsymbol{\cap}$	
u	-3		ш	u	ш	u	

Product Description

BYNEL® Series 2200 resins are modified ethylene acrylate resins. They contain a temperature stable ester which makes them functional in high temperature coextrusions. They are available in pellet form for use in conventional extrusion and coextrusion equipment designed to process polyethylene (PE) resins.

Restrictions

Material Status

· Developmental: Active

Typical Characteristics

Characteristics / Benefits

Physical properties of BYNEL Series 2200 resins are typical of polyethylene/acrylate copolymer resins with similar density and melt index values.

Applications

BYNEL 2200 series resins adhere to a wide variety of materials. They are most often used to adhere to PE, PP, PET and paper.

Typical Properties

Nominal Values Physical Test Method(s) Density () 0.94 g/cm³ ASTM D792 ISO 1183 Melt Flow Rate (190°C/2.16kg) 8.0 g/10 min **ASTM D1238** ISO 1133 Thermal **Nominal Values** Test Method(s) Melting Point (DSC) 92°C (198°F) **ASTM D3418** ISO 3146 54°C (129°F) **ASTM D1525** ISO 306 Vicat Softening Point Additional

Adhesive Evaluation

The performance of any adhesive resin should be evaluated within the context of the application. The adhesive is designed to bond materials that would not ordinarily adhere to each other. In most cases, peel strength is used as a measure of performance. Although this is a convenient test, peel strength is affected not only by adhesion, but also by peel angle, separation rate, temperature, and tensile and modulus properties of the materials, and often by the time elapsed since the formation of the bond. Post-treatment of the multi-layer structure, such as heat sealing, thermoforming or orientation can also affect peel strength. If peel strength is used as a measure of adhesive performance, it is imperative that

peel strength be evaluated not only at the time of manufacture, but throughout the life of the product and under all the various conditions to which the structure will be exposed. Only then can the performance of the adhesive be related to peel strength.

Processing Information

General

Maximum Processing Temperature 310°C (590°F) General Processing Information

The temperature profiles shown below are for initial evaluations of BYNEL adhesive resins in the 2200 series. These profiles are designed to provide adequate exposure time of the adhesive resin to elevated temperatures.

Because the BYNEL 2200 Series resins have low softening points, it is a good idea to run the rear of the extruder as cool as possible, then build quickly to the melt temperature. Water cooling of the screw and/or hopper feed throat may help avoid bridging problems.

Specifically, in coextrusions with thermally sensitive resins such as EVOH or EVA. we suggest that the maximum melt temperature be limited to 235C (455F) to guard against overheating the EVOH or EVA. If adhesion results are adequate, we suggest evaluating even lower melt temperatures such as 210C - 220C (410F -

For coextrusion with polyamides, polyolefins or other thermally stable resins, the melt temperature can be higher. We suggest a maximum melt temperature of 310C (590F). This should provide acceptable bond strengths and film quality under almost all coextrusion conditions. If adhesion results are adequate, melt temperatures can be lowered. While it is possible to extrude BYNEL 2200 series resins as high as 310C (590F), such high extrusion temperatures, particularly when coupled with long residence times, may result in some film imperfections. In certain streamlined extrusion operations, where residence times are short, it may be possible to use temperatures higher than 285C (545F).

Variation of these suggested temperature profiles may be appropriate depending upon the screw configuration, potential extruder horsepower limitations, potential back pressure limitations, the need to match rheologies and/or the stability of the other resins in the coextrusion. Film quality will also depend upon the residence time of the adhesive resin in the system. Dead spots may result in localized overheating and should be avoided by ensuring the flow path for the adhesive is as streamlined as possible.

We suggest using any standard polyolefin working screw when extruding BYNEL 2200 series resins. Excessively deep flights should be avoided as they might result in poor melting of the adhesive resin. It is also important to properly size the extruder for the output desired. Running large extruders at very low RPMs should be avoided.

For producing monolayer adhesive films with BYNEL 2200 adhesive resins. extrusion conditions commonly used for converting ethylene acrylate resins into films can be employed.

When extruding BYNEL 2200 series resins as an exposed outer surface in a multi-layer coextrusion, problems related to the tackiness and high coefficient of friction of these products may be evident. In this case, it is suggested that the extrusion temperature be lowered to 160C - 210C (320F - 410F) or less. Addition of slip and silica-based antiblock packages may also be appropriate to prevent blocking and improve film handling, although these additive packages may modify the resin's bonding characteristics.

If the coextrusion process is stopped for short periods of time, the screw in the adhesive extruder should be kept turning at a low RPM level. For a permanent shutdown, the BYNEL adhesion resin should be purged out using an available polyethylene resin run at the same extrusion temperature used during the extrusion process of the adhesive resin. Making frequent changes in screw speed during the shutdown process and subsequent start-up will help remove the previous material from the system more effectively. Sometimes upon start-up of the adhesive resin, excessive amounts of gel may be observed. This may be due to the natural ability of the adhesive resin to act as a purging compound. In this case, continued extrusion will eventually clear up the problem.

Extrusion Coating/Lamination Processing

Nominal Values

Extrusion Coating / Lamination Processina

Proposed Extruder Set Temperatures

Feed Zone	160°C	(320°F)
Second Zone	210°C	(410°F)
Third Zone	260°C	(500°F)
Fourth Zone	285°C	(545°F)
Fifth Zone	285°C	(545°F)
Adapter Zone	285°C	(545°F)
Die Zone	285°C	(545°F)

FDA Status Information

BYNEL® 22E757 Adhesive Resin complies with Food and Drug Administration Regulation 21 CFR 177.1340(a) - - Ethylene-methyl acrylate copolymer resins, subject to the limitations and requirements therein. This Regulation describes polymers that may be used in contact with food, subject to the finished food-contact article meeting the extractive limitations under the intended conditions of use, as shown in paragraph (b) of the Regulation.

The information and certifications provided herein are based on data we believe to be reliable, to the best of our knowledge. The information and certifications apply only to the specific material designated herein as sold by DuPont and do not apply to use in any process or in combination with any other material. They are provided at the request of and without charge to our customers. Accordingly, DuPont cannot guarantee or warrant such certifications or information and assumes no liability for their use

Regulatory Information

Safety & Handling

For information on regulatory compliance outside of the U.S., consult your local DuPont representative.

For information on appropriate Handling & Storage of this polymeric resin, please

refer to the Material Safety Data Sheet..

A Product Safety Bulletin, Material Safety Data Sheet, and/or more detailed information on extrusion processing and/or compounding of this polymeric resin for specific applications are available from your DuPont Packaging and Industrial Polymers representative.

Read and Understand the Material Safety Data Sheet (MSDS) before using this product

Regional Centres

DuPont operates in more than 70 countries. For help finding a local representative, please contact one of the following regional customer contact centers:

Americas

Fax:

DuPont Company Chestnut Run Plaza – Bldg. 730 974 Centre Road Wilmington, Delaware 19805 U.S.A. Toll-Free (USA): 1-800-628-6208 Telephone: 1-302-774-1000

DuPont do Brasil, S.A. Alameda Itapecuru, 506

1-302-355-4013

06454-080 Barueri, SP Brasil Telephone: +55 11 4166 8000

Asia Pacific

DuPont China Holding Co., Ltd. Shanghai Branch 399 Keyuan Road, Bldg. 11 Zhangjiang Hi-Tech Park Pudong New District, Shanghai P.R. China (Postcode: 201203) Telephone +86 21 3862 2888 Fax +86-21-3862-2889

Europe / Middle East / Africa

DuPont de Nemours Int'1. S.A. 2,Chemin du Pavillon Box 50 CH-1218 Le Grand Saconnex Geneva, Switzerland Telephone +41 22 717 51 11 Fax +41 22 717 55 00 Fax: +55 11 4166 8736

http://bynel.dupont.com

The data listed here fall within the normal range of properties, but they should not be used to establish specification limits nor used alone as the basis of design. The DuPont Company assumes no obligations or liability for any advice furnished or for any results obtained with respect to this information. All such advice is given and accepted at the buyer's risk. The disclosure of information herein is not a licence to operate under, or a recommendation to infringe, any patent of DuPont or others. Since DuPont cannot anticipate all variations in actual end-use conditions, DuPont makes no warranties and assumes no liability in connection with any use of this information.

CAUTION: Do not use DuPont materials in medical applications involving implantations in the human body or contact with internal body fluids or tissues unless the material has been provided from DuPont under a written contract that is consistent with DuPont policy regarding medicalk applications and expressly acknowledges the contemplated use. For further information, please contact your DuPont representative. You may also request a copy of DuPont POLICY Regarding Medical Applications H-50103-3 and DuPont CAUTION Regarding Medical Applications H-50102-3.

Copyright © 2009 DuPont. The DuPont Oval Logo, DuPont™, The miracles of science™, and trademarks designated with "®" are registered trademarks or trademarks of E.I. du Pont de Nemours and Company or its affiliates. All rights reserved.

This data sheet is effective as of 08/07/2010 04:35:17 PM and supersedes all previous versions.